

Adjust-A-Wall™ – TRACK AND ROLLER CURTAIN PARTITIONS



Warehouse Partition
Blue vinyl laminate
with clear transparent
window



Welding Enclosure - Yellow vinyl laminate
with orange tinted transparent window

Adjust-A-Wall™ provides protection or partitioning when you need it and rolls easily out of the way when you don't need it. Workers painting, sanding, washing, welding, grinding, cutting, or assembling can work side by side with people needing a clean environment or an adjustable wall.


- Dramatically increase usable workspace at a fraction of the cost of permanent structures
- Cost effective, easy to order and easy to install. It increases efficiency and promotes safety
- Widely used for wash bays, departmental workstations, storage areas, assembly lines, paint, primer & prep areas, welding and grinding booths, and test labs

Adjust-A-Wall™ consists of a sturdy 16-gauge galvanized steel track system with durable, smooth rolling nylon roller-hooks and a heavy-duty vinyl curtain partition.




Each curtain has Velcro® closures sewn along vertical edges to provide seamless connections and easy access to enclosed areas. A weighted chain is sewn into bottom hem to hold curtains in place from wind or drafts.

ADJUST-A-WALL™ MOUNTING HARDWARE


Suspended Mount





Attach track mounts to chain, cable, threaded rod or angle iron.
Vertical (Chain or Beam)




Ceiling Mount




Attach track mount brackets flush to ceiling, floor joists or to bottom of a beam




Wall Mount





Attach track mounts to header walls above openings or use wall end brackets to brace or stabilize track



Floor Mount



Attach track mounts to floor columns erected from heavy-duty 12" floor base.



Straight Tracks, Roller-hooks, & Accessories



2-Wheel
Nylon
Roller-hooks
44600



Roller End Stop
44705



Track Splice
44500



Straight Track
44003 – 3' 44007 – 7' 44011 – 11'
44004 – 4' 44008 – 8' 44012 – 12'
44005 – 5' 44009 – 9'
44006 – 6' 44010 – 10'

CUSTOM ADJUST-A-WALL™ SYSTEMS

Design the custom system that best suits your needs.
Easy to Order, Easy to Install...

How to order custom Adjust-A-Wall™ Systems:

1. Select type of curtain material (vinyl laminate, tinted transparent, clear vinyl, cotton duck) from page 38.
2. Select desired colors (vinyl laminate, tinted transparent or combination of colors) from page 38.
3. Measure the height and order to exact height required. (+/- 1" tolerance). Floors are not always even, take measurement from highest point of floor. Factory deducts 2" from curtain height to allow for track and roller-hooks.
4. Determine the configuration of the Adjust-A-Wall System....straight run, two-sided "L" shape, three-sided "U" shape, four-sided enclosure "O" shape, or multiple stations (sketches are always helpful). Total up the number of linear feet (running length). Custom Partitions are sold by the linear foot of hardware required.
5. Determine installation method: **Suspended** (from overhead by cable, chain or threaded rod). **Ceiling, Wall or Floor Mount.** (Suspended is most common). See page 44 for mounting options.

The factory will determine and provide all necessary connectors, track and hardware based on the installation mounting method and configuration chosen. (Hardware is not provided with replacement curtains). Vinyl strip curtains can be included in combination with your Adjust-A-Wall System. Contact a Steiner Team Member for custom solutions.

Note: Minimum 2" shall be deducted from curtain height to allow for track & rollers. Normal tolerance is +/- 1" 10% is added to curtain width for proper drape.



Adjust-A-Wall™

	Custom Partitions with Hardware	Replacement Curtains Only
Height		
6'	A4406	AWCOM-06
7'	A4407	AWCOM-07
8'	A4408	AWCOM-08
9'	A4409	AWCOM-09
10'	A4410	AWCOM-10
11'	A4411	AWCOM-11
12'	A4412	AWCOM-12
13'	A4413	AWCOM-13
14'	A4414	AWCOM-14
15'	A4415	AWCOM-15
16'	A4416	AWCOM-16

EASY TO INSTALL

The most popular method of erecting Adjust-A-Wall™ Partition Systems is suspension mount. Track is hung from overhead (beams or trusses) supported from chain, cable, threaded rod or angle iron (not provided). Upon installation of chain or other supports, the appropriate track connectors (Chain or Threaded Rod type) are attached to track at approximate 4' – 8' intervals to suspend the track. Once track is suspended in place at height desired, roller-hooks shall be inserted into track slot (1 roller per foot of curtain). Close track slot by installing end stop at each end of track. Hang the partition by inserting hooks through brass grommets along top edge of curtain. Curtains should reach approximately 1" or more above floor for smooth, fluid movement.


MODULAR ADJUST-A-WALL™ PARTITION SYSTEMS

Modular Partition Systems allow you to create add-on sections for use as a single divider, or create enclosures by adding on straight or curved sections.

Each section contains a Blue/Clear/Blue curtain, straight track or curve track, roller-hooks, and suspended mount connectors. Choose by height and section width desired. Add on more sections to enlarge or reconfigure your enclosure or partition needs.

How to order Modular Adjust-A-Wall™ Systems:

- 1) Determine the height of your partition system
- 2) Select the sizes (6', 8', 10') of straight track or (4') curve sections needed to make a partition system.



MODULAR KITS (Curtains & Hardware)				
Height	6' Straight Section	8' Straight Section	10' Straight Section	90° Curve Section
8'	AWC68	AWC88	AWC08	AWCC8
9'	AWC69	AWC89	AWC09	AWCC9
10'	AWC60	AWC80	AWC00	AWCC0
11'	AWC61	AWC81	AWC11	AWCC1
12'	AWC62	AWC82	AWC02	AWCC2



Note: 90° Curve sections have a 4-foot radius that provides 2 feet of length on each side of the curve. For example, if a 10' x 10' L-shaped partition is desired (i.e. that is 10' on each side), you should order two 8' Straight sections and one (4') Curve Section.